

KERN IXC 60K-3

KERN

Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation



Load cell connection 4-wire

Approval

CE mark ✓

Display

Display type LCD
 Display type LCD with backlight
 Display screen size 160×60 mm
 Display backlight ✓
 Display digit height 48 mm
 Languages of the user interface English
 Symbol language

Construction

Dimension display device (W×D×H) 232×150×80 mm
 Dimensions weighing platform (W×D×H) 400×300×114 mm
 Material display housing stainless steel
 Material weighing plate stainless steel
 Material platform steel, varnished
 Dimensions weighing surface (W×D) 400×300 mm
 Display device cable length 3 m
 Allowed cable length display device [Max] 3 m
 Material load cell(s) aluminium
 Load cells - number 1
 Levelling feet adjustable ✓
 Wall mount ✓

Functions

Number of keys for operation 7
 Auto-off interval(s) in mains power mode off
 Auto-off interval(s) in battery mode/rechargeable battery mode 5 min
 2 min
 1 min
 30 min
 60 min
 30 sec
 Capacity display ✓
 PreTare function ✓
 Tare function manual (multi)
 Hold function ✓
 Percentage determination ✓
 Counting function ✓
 Tolerance weighing ✓

Category

Brand KERN
 Product category Industrial scale
 Product group Platform scale
 Product family IXC

Measuring System

Construction type of the scale Single-range balance
 Number of weighing ranges 1
 Weighing system Strain gauge
 Weighing capacity [Max] 60 kg
 Readability [d] 0,002 kg
 Resolution 30.000
 Linearity ± 0,006 kg
 Reproducibility 0,002 kg
 Default unit kg

Units

kg
 g
 lb
 ffa
 PCS
 %

Adjustment options Adjusting with external weight
 Recommended adjusting weight 60 kg (M1)
 Possible calibration points 60 kg
 Stabilization time 3 s
 Warm-up time 120 min
 Eccentric loading at 1/3 [Max] 0,006 kg
 Maximum creep (15 minutes) 8 g
 Maximum creep (30 minutes) 16 g
 Loadcell type aluminium IP65 silicone-coated

KERN IXC 60K-3



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory)
	Bluetooth (optional, factory)
	Ethernet (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional, factory)
	analogue (4 - 20 mA) (optional, factory)
Bluetooth BLE (v4.0) (optional, factory)	
USB-Device (optional, factory)	
IP protection - complete device	-
IP protection - display	IP68
IP protection - load cell	IP65
IP protection - platform	no IP protection

Counting	
Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000

Power Supply	
Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO

Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-Ion

Environmental conditions	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	500×635×222 mm
Net weight	10,5 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	14 kg
Shipping weight	14,1 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517


KERN IXC 60K-3



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

Pictograms

STANDARD



OPTION



FACTORY

